PRODUCT INFORMATION



TecPleat LD filter elements are designed for applications requiring very high flow rates & are suited equally as pre-filters or final polishing filters where membrane filtration is not required.

TecPleat LD use a specially designed spacer layer on the upstream of the filter media which helps maintain an open flow path to the entire surface area. This maximises dirt holding capacity and minimises pressure drop across the filter.

Absolute micron ratings are tested to Beta 5000 using industry standard single pass OSU-F2 test procedure with ISO 12103 part 1 A2 fine and A4 coarse test dust as appropriate.

Polypropylene hardware combined with either polypropylene or glass fibre filtration media and thermal bonded construction ensures wide chemical compatibility, minimising extractables and ensuring product integrity in demanding applications.

Also available as an All Welded Stainless Steel option. No polymeric material or adhesives are involved in the construction (except the sealing oring). TIG Welded construction. Suitable for high temperatures and aggressive chemical applications.

Polypropylene cartridges have been independently tested for extractables and meet the requirements for food consumption regulation as detailed in EC 1935/2004 and incorporating 10/2011. Materials used are listed FDA CFR21 part 177.



PROSEP



Available in three hardware options as follows to suit varying levels of process conditions

- Polypropylene hardware with either pleated Glass Fibre or Polypropylene media
- Polypropylene endcaps with stainless steel cage with either pleated Glass Fibre or Polypropylene media
- All Welded Stainless Steel steel endcaps, cage & media (either sintered fibre or sintered mesh)

Prosep Filter Systems Ltd Unit G19, River Bank Way, Lowfields Business Park, Elland, West Yorkshire HX5 9DN

Phone: 01422 377367 email: sales@prosep.co.uk www.prosep.co.uk

for all your filter requirements



PRODUCT INFORMATION

TECPLEAT ALL WELDED STAINLESS STEEL LARGE DIAMETER PLEATED CARTRIDGES

Also available as an All Welded Stainless Steel version with no use of glues or adhesives the AWSS version of the High Flow Pleat provides the solution to compatibility issues whilst maintaining excellent flow rates. Manufactured entirely out of 316L stainless steel (except for the sealing o-ring) they are especially suited to high temperature applications or where chemical compatibility is an issue with polypropylene.

Materials of Constructions (AWSS version)


- Filtration Media Sintered steel mesh
- Sintered steel fibre
- Endcaps 316L stainless steel
 - Cage 316L stainless steel
- Seals As standard version options

• Construction TIG Welded Recommended Operating Conditions

Operating Temperature

- -150°C to 300°C (seal material dependent)
- **Maximum Differential Pressure**
- 3.0 barg
- **Recommended Changeout Pressure**
- 1.5 barg





Designed to be dimensionally equivalent to the standard High Flow elements these AWSS TecPleat are designed to fit standard High Flow Housings.

Micron Ratings Available

- **SSF Sintered Steel Fibre** (absolute rated) available in the following micron ratings 3, 5, 10, 15, 20, 30, 40, 60
- SSM- Sintered Steel Mesh (nominally rated) available in the following micron ratings

Prosep Filter Systems Ltd Unit G19, River Bank Way, Lowfields Business Park, Elland, West Yorkshire HX5 9DN

Phone: 01422 377367 email: sales@prosep.co.uk www.prosep.co.uk

for all your filter requirements

PRODUCT INFORMATION

TECPLEAT LARGE DIAMETER PLEATED CARTRIDGES

Materials of Constructions

- **Filtration Media** Polypropylene •
- **Glass Microfibre**
- Polypropylene Support Layers
- Polypropylene Endcaps
- Cage
- Seals
- Polypropylene Nitrile EPDM Silicon Viton

PTFE

Recommended Operating Conditions Maximum Temperature


80°C •


Maximum Differential Pressure

- 3.5 barg maximum @ 20°C •
- 1.8 barg maximum @ 65°C
- 1.0 barg maximum @ 80°C

Recommended Changeout Pressure


1.5 barg @ 20°C







Micron Rating
045—0.45
01 - 1
05 - 5
10 - 10
25 - 25
50 - 50
100 - 100



Filter Media
PP - Polypropylene
GF - Glass Fibre
SSF - SS fibre
SSM—SS Mesh

PROSEP **FILTER SYSTEMS**

Refer to page two for micron ratings for SSF and SSM cartridges

Prosep Filter Systems Ltd Unit G19, River Bank Way, Lowfields Business Park, Elland, West Yorkshire HX5 9DN

Phone: 01422 377367 email: sales@prosep.co.uk www.prosep.co.uk

20

40

60

for all your filter requirements